



"A leading worldwide supplier of high efficiency filters for a variety of industries and applications."

HEATED FILTER ASSEMBLIES

UFS Heated Filter assemblies are design specifically for engine testing, continuous emissions monitoring and stack gas applications. Our simple design uses a silicone heating jacket which is form fitted to eliminate "cold spots" and provide a fast, even transfer of heat. If the heater ever needs maintenance the silicone heating jacket can easily be replaced in the field. The entire unit is encased in durable high temperature thermal plastic case good up to 450°F which can be mounted either vertical or horizontal. We offer 3 standard sizes to accommodate a wide range of flows to suit each specific application. All of our units use industry standard cartridges which help minimize inventory. Each of our Heated Filter Assemblies are available with either a J-Type or K-Type Thermocouple. We also offer the option of dual thermocouples in case of a thermocouple failure. The housing is designed with a 1/4 turn bayonet type handle to make changing the filter cartridge simple and safe even at high temperatures.



Features:

- User Friendly Design
- Rugged Construction
- Choice of K-Type or J-Type Thermocouple
- Accepts Industry Standard Filter Cartridges
- Quick Release Bayonet-Type Closure
- 450°F Maximum Temperature (232°C)

Applications:

- Automotive Emission Testing
- Continuous Emissions Monitoring
- Stack Gas Testing

TECHNICAL INFORMAT J-TYPE Thermocouple	HM-H130STR-HJ	HM-H140STR-HJ	HM-H254STR-HJ
K-TYPE Thermocouple	HM-H130STR-HK	HM-H140STR-HK	HM-H254STR-HK
Maximum Pressure (psig)	30	30	30
Maximum Temperature (°F)	450	450	450
Internal Volume (cc)	85	235	1030
Weight of Housing (lbs)	9.0	13.0	24.0
Principle Dimensions: (inches)			
Diameter of Heat Module	4.75	4.75	6.63
Overall Length with Handle	11.50	16.00	19.00
Overall Length without Handle	8.50	13.00	16.00
Base Plate Dimensions	6.00 Square	6.00 Square	8.00 Square
Element Removal Clearance	5.34	9.58	12.72
Filter Element Codes: (1)			
Disposable (Silica) Element	25-64-□S	25-178-□S	51-250-□S
Disposable (PVDF) Element	25-64-□K	25-178-□K	51-230-□K
Disposable (Acid-Washed) Element	25-64-□S-AW	25-178-□S-AW	51-230-□S-AW
Stainless Steel Element	SS-25-64-□	SS-25-178-□	SS-51-230-□
Volts	120	120	120
Amps	1.5	1.5	1.5
Watts	180	180	180
Frequency	50/60 Hz	50/60 Hz	50/60 Hz
Housing Port	1/4″	1/4"	1/2″
	Tube Stubs Supplied per Co	ustomer Specifications	

HEATED FILTER ASSEMBLIES

Heated Module Controller:

A complete packaged solution may be provided with our off -the -shelf digital temperature controller that maintains accuracy of +/- 1%. Once the controller reaches its set point it will turn off and not turn on again until the temperature drops by 5°F. As a safety feature the controller will sound an audible alarm if the temperature exceeds 15°F above the set point. This option allows us to provide a turnkey system to meet your demands.



Two Models Available:

Model #HM-Controller-J Model #HM-Controller-K

Specifications:

- 120
- 15 amps
- Digital on/off controller
- Units in °F
- Input power cord 6 feet (1.8m) long with standard plug -120 VAC: NEMA 5-15
- Output Receptacle:
- -IP 67 four-pin (NEMA 6P equivalent) (plug assembly included)
- Audible alarm
- Type K thermocouple mini and standard connector input
- Average accuracy of ±1% FS
- Resolution: 1°
- Hystersis: 5°
- Suitable for outdoor use (must be mounted vertically)
- Operating exposure temperatures: 14 to 131°F
- Storage exposure temperatures: -4 to 176°F
- Mounting feet included
- Optional mounting bracket kit ideal for tote tank / IBC applications

Ordering information:

To order, please contact us at 1-800-311-5561. We inventory an extensive range of components to provide fast delivery of complete turnkey systems. Filter housings, silicone heater jackets, and controllers are stocked to expedite our services. Your fitting/connection requirements will need to be specified to finalize your order. Lastly, the module is tested for 24 hours prior to shipping to guarantee performance.